


The high magnetic field sensitivity, accurate calibration, high stability and high signal output of the Sentron CSA-1V Hall effect IC enable it to be conveniently used to monitor the extended fields from magnetic items and electric equipment. As a demonstration of the CSA-1V capability, three CSA-1V with sensitive axes mutually perpendicular, are combined in a compact module as the MFS-3A. Three output voltages  $V_x = S \cdot B_x$ ,  $V_y = S \cdot B_y$  and  $V_z = S \cdot B_z$  are generated proportional to the magnetic flux density components  $B_x$ ,  $B_y$  and  $B_z$  with the sensitivity  $S = 280\text{mV/mT}$  over the field range of  $\pm 7.3\text{mT}$ . This enables calculation of the total magnetic flux density,  $B = (B_x^2 + B_y^2 + B_z^2)^{1/2} = (V_x^2 + V_y^2 + V_z^2)^{1/2}/S$ .



### Specifications

- \* Measures  $B_x$ ,  $B_y$ ,  $B_z$
- \* Suitable for environmental magnetic fields
- \* Field range:  $\pm 7.3\text{mT}$  ( $\pm 73\text{G}$ )
- \* Resolution:  $\pm 10\mu\text{T}$  ( $\pm 0.1\text{G}$ )
- \* Three linear analog outputs  $V_x$ ,  $V_y$ ,  $V_z$  of 0.5V to 4.5V
- \* Sensitivity:  $S = 280\text{mV/mT}$
- \* Accuracy:  $\pm 3\%$
- \* Angular alignment:  $\pm 3\text{deg}$
- \* Frequency response dc to 100kHz (-3dB)
- \* Small size: 10 x 13.5 x 12mm (0.39 x 0.53 x 0.47inch)
- \* Low weight: 2.5g (0.1oz)
- \* Low power: 36mA max at 5V

### Applications:

- \* Quality assurance of magnetized materials and items such as sealing strips and permanent magnets by fast and complete characterization of the external magnetic field.
- \* Detection/separation of magnetic and non-magnetic materials by monitoring the modification of the local or imposed field caused by magnetic item/items.
- \* Non-contact, non-invasive and continuous "Condition Monitoring" of electrical motors, generators, transformers or inductors by comparing the amplitudes of selected external or "leakage" field spectral components with initial or reference values. Quality assurance of electrical components by leakage field measurement.
- \* Independent monitoring of the ON/OFF status of large magnets with extended fringing fields. The MFS-3A output can be used to operate warning indicators and/or interlocks. Resolution of  $\pm 10\mu\text{T}$  readily allows measurement of the  $500\mu\text{T}$  (5G) safety level applicable to Magnetic Resonance Imagers (MRI).
- \* Wearable, battery operated "Personal Magnetic Field Detector" to immediately generate a warning to the wearer that they have entered a region of increased magnitude magnetic field.
- \* Magnetic field detection and warning or interlock to be incorporated in magnetically sensitive equipment such as time standards or patient support equipment that may be used in the fringe field of an MRI or other large magnet.

